

# Tempered flat steel healds

with J-, C- and O-shaped end loops

Non-tempered flat steel healds

with O-shaped end loops

### Tempered flat steel healds


Functionally efficient healds are small in size but they are critical components when it comes to the performance and productivity of a weaving machine.

### **Advantages of Groz-Beckert healds:**

- Suitable for all weaving machines
- High wear resistance due to lightweight and durable material that is suitable for extreme applications
- Minimal friction and damage to warp yarns resulting in reduced contamination of weaving harness
- Gentle transitions during shed change with the OPTIFIL thread eye
- Ideal performance in combination with automatic drawing-in systems

## Advantages of the OPTIFIL thread eye:

- Densities up to 30% higher than the standard thread eye
- Gentle transitions during shed changes
- Increased machine efficiency
- Reduced warp end breakage
- Increases in machine speed




# **GROZ-BECKERT**

#### **Groz-Beckert KG**

Parkweg 2, 72458 Albstadt, Germany Phone +49 7431 10-0, Fax +49 7431 10-2777 contact-weaving@groz-beckert.com www.groz-beckert.com

### Tempered flat steel healds



#### **SOLOPUR** healds



#### **DUOMIX** healds




#### **Healds micro PLUS:**

The micro PLUS healds offer an ultra-fine surface finish which is always required for successful weaving of sensitive microfibres and finest filament yarns.

All micro PLUS healds are manufactured with the OPTIFIL thread eye.

# Surface finish of weaving heald in thread



# **GROZ-BECKERT**

## **Tempered flat steel healds**

Suitable for warp	counts				Maximum density per heald frame <sup>1)</sup>								
					Standard - thread eye OPTIFIL- thread eye								
					SOLOPUR SIMPLEX	DUOMIX DUPLEX DUOREV DUODIF	SOLOPUR	DUOMIX DUODIF DUOWIN DUOREV	Cross section	Thread eye		Designation	End loop
Tex	Nm	Td	NeB	NeK	per cm		per cm		mm	mm			
30	34	300	20	30		20		28	5,5 x 0,25	F F 1 0		CDOD® EVEDA	J
30					12	18	15	23	5,5 x 0,30	5,5 x 1,2		GROB® EXTRA	
72	14	650	8	12	8		10		5,5 x 0,30	6,5 x 1,8	_	GROB® EXTRA	
					7		9		5,5 x 0,38				
						12		15	6 / 7,2 x 0,30				
250	4		2		6		8		5,5 x 0,30	6,5 x 2,5		GROB® EXTRA	
230	4		2		6		8		5,5 x 0,38			GRUD® EXTRA	
250	4		2	4	10				5,5 x 0,30	8,0 x 3,8		GROB® EXTRA	
230	, T		-	7	8				5,5 x 0,38			GIIOD® EXTIIA	
	34	300	20	30		20		28	5,5 x 0,25			GROB® EXTEX	
30					12	18	15	23	5,5 x 0,30	5,5 x 1,2			
						15		17	5,5 X 5,55			GROB® IMEXTEX	С
72	14	650	8	12	8		10		5,5 x 0,30	6,5 x 1,8		GROB® EXTEX	
					7		9		5,5 x 0,38				
250	4		2		6		8		5,5 x 0,30	6,5 x 2,5		GROB® EXTEX	
			_		6		8		5,5 x 0,38		UNUD ENTER		
250	4		2	4	10				5,5 x 0,30	8,0 x 3,8		GROB® AMEXTEX	
			_		8				5,5 x 0,38			- ,	
30	34	300	20	30		20		28	5,5 x 0,25 5,5 x 0,30	5,5 x 1,2		GROB® EXO	0
						18		23					
				10		15	10	17			_	GROB® IMEXO	
72	14	650	8	12	8		10		5,5 x 0,30	6,5 x 1,8		GROB® EXO	

# Non-tempered flat steel healds

125	8		5	7	8			3,5 x 0,40	7,0 x 2,0	GROB® 0	
						20		2,2 x 0,30			$\cap$
30	34	300	20	30			24	2,6 x 0,25	5,5 x 1,2	GROB® EXO	U
							17	2,8 x 0,30			

<sup>1)</sup> The density corresponds to the average standard applications. Deviations depend on the number of heald frames and warp yarn specifications.

Overview of the most common healds, further types are available upon request.



Meaving | EN | 05.2019